

618

VIPR - Acetylene

TECHNICAL SPECIFICATIONS:

- 1 stage regulating system (0 - max. 1,5 bar)
- European Patent No. EP2215537
- Pressure indicator (0-40 bar) *Built into the valve body*
- Pressure gauge (0-2,5 bar) *Built into the valve body*
- Filter incorporated to protect the regulating unit
- Standard flow rate $Q_1=30$ l/min

For further technical specifications on this valve please see reverse.



*Optional
Protective guard*



80 years of proven experience

Discover more of our products at: www.bmv.dk

TECHNICAL SPECIFICATIONS: 618 VIPR - Acetylene

About this valve

The Müller type 618 industrial VIPR sets new standards with its new innovative design. It is equipped with a 1 stage regulating unit. The regulating unit has a patented balanced system allowing you to change the flow settings by applying a constant torque. Pressure gauges are incorporated into the main valve body for better protection.

For easy maintenance of the regulating unit, the main valve can be shut off and the complete unit can be replaced without further disassembly.

The valve is manufactured on state in Denmark of the art manufacturing equipment, and the quality is monitored throughout the entire process. The valve is assembled on a automated assembly line using Helium as media for accurate leak testing. The valve is subjected to a 100% functional test on the assembly line with complete records of all test results, ensuring full data traceability. When the valve has passed all tests on the assembly line, it is allocated a unique serial number relating to the recorded test data, giving you a world class industrial VIPR!

BAM Approved: according to ISO 22435

Working pressure: 18 bar

Inlet connection: 25E, 25ES, W31.3, W29.2, W36 or other on request

Outlet connection: Quick connect EN 561, screw connection ISO 3253, or other on request

Filling connection: DS2404, DIN, NEN, AFNOR, UNI, NBN, CGA, BS, AS, ISO 5145 or other on request

Outlet pressure: adjustable 0 - max 1,5 bar

He leak tested: leak rate of $\approx 2 \times 10^{-3}$ mBAR x l/sec (6 cm³/h)

Valve weight: 1,9 kg

Valve dimension, height over cylinder: 110 mm (approx)



Opening/closing to cylinder: Handwheel

Regulation of flow: Handwheel


Not for medical use

Contact our Sales Department to place your order:


Phone: +45 73 42 12 12 · info@bmvd.dk



Regulationcurve 618-VIPR valve (Acetylene gas)



Regulationcurve 618-VIPR valve (Acetylene gas)



Müller
GAS EQUIPMENT A/S
GAS CONTROL SOLUTIONS

Müller Gas Equipment A/S

Mommarkvej 7-11 · Vollerup · DK-6400 Sønderborg

Telefon: +45 73 42 12 12 · Fax: +45 73 42 12 07 · email: info@bmvd.dk · www.bmvd.dk

See our online
catalogue

